



19 3006 S 10



19 3006 S 22



19 3006 S 13



19 3006 S 20



19 3006 S 30



19 3006 S 33



19 3006 S 11



19 3006 S 01



19 3006 S 15



19 3006 S 23

- Movement:** Hour, Minute, Small Second Hands  
Control by 3 Motors
- RF Link:** Connect to IOS and Android mobile phone
- Features:** STOPPER, STEP, TIME/DATE,  
TOUCH HEART RATE,  
SLEEP & ALARM ALERT
- Stopper:** 1 sec Resolution up to 12 Hours  
(Operation by App)  
Daily Steps from 1 to 12000 Steps  
2 Hands, Hour/Minute/Date/Day/Step  
1st to 31st
- Heart Rate:** ECG Finger Touch Heart Rate  
works between 40-190BPM
- Sleep Alert:** Piezo Sound (Operation by App)
- Alarm Alert:** Piezo Sound (Operation by App)
- Incoming Phone:** Piezo Sound / LED Flashing
- Incoming Message:** Piezo Sound / LED Flashing
- Battery:** Lithium Battery, CR2025
- Battery Life:** 5 months typ, 8 months Max.
- No. of Button:** 1

## SIZE



Battery Caseback



Optical HR Caseback

## THICKNESS



12.00mm



13.50mm

Optical  
Heart Rate



19-L049H P 33



19-L049H P 30



19-L049H P 35



19-L049H P 66



19-L049H P 50

Scale 1:1



19-L049H P 55



19-L049H P 77



19-L049H P 60

Scale 1:1



19-L049H P 00



19-L049H P 01

<b>Movement:</b>	Hour, Minute, Small Second Hands Control by 3 Motors
<b>RF Link:</b>	Connect to IOS and Android mobile phone
<b>Features:</b>	STOPPER, STEP, TIME/DATE, TOUCH HEART RATE, SLEEP & ALARM ALERT
<b>Stopper:</b>	1 sec Resolution up to 12 Hours (Operation by App) Daily Steps from 1 to 12000 Steps 2 Hands, Hour/Minute/Date/Day/Step 1st to 31st
<b>Heart Rate:</b>	ECG Finger Touch Heart Rate works between 40-190BPM
<b>Sleep Alert:</b>	Piezo Sound (Operation by App)
<b>Alarm Alert:</b>	Piezo Sound (Operation by App)
<b>Incoming Phone:</b>	Piezo Sound / LED Flashing
<b>Incoming Message:</b>	Piezo Sound / LED Flashing
<b>Battery:</b>	Lithium Battery, CR2025
<b>Battery Life:</b>	5 months typ, 8 months Max.
<b>No. of Button:</b>	1

## SIZE



Battery Caseback



Optical HR Caseback

## THICKNESS

