



19-1007L S 33



19-1007L S 20



19-1007L S 13



19-1007L S 10



19-1007L S 31

Scale 1:1



19-1007L S 33



19-1007L S 22



19-1007L S 21



19-1007L S 16

Scale 1:1




19-1007L S 11

- Movement:** Hour, Minute, Small Second Hands
Control by 3 Motors
- RF Link:** Connect to IOS and Android mobile phone
- Features:** STOPPER, STEP, TIME/DATE,
TOUCH HEART RATE,
SLEEP & ALARM ALERT
- Stopper:** 1 sec Resolution up to 12 Hours
(Operation by App)
- Step:** Daily Steps from 1 to 12000 Steps
- Time:** 2 Hands, Hour/Minute/Date/Day/Step
- Date:** 1st to 31st
- Heart Rate:** ECG Finger Touch Heart Rate
works between 40-190BPM
- Sleep Alert:** Piezo Sound (Operation by App)
- Alarm Alert:** Piezo Sound (Operation by App)
- Incoming Phone:** Piezo Sound / LED Flashing
- Incoming Message:** Piezo Sound / LED Flashing
- Battery:** Lithium Battery, CR2025
- Battery Life:** 5 months typ, 8 months Max.
- No. of Button:** 1

SIZE



THICKNESS





19 009L P 33



19 009L P 30



19 009L P 32



19 009L P 44



19 009L P 40

Scale 1:1



19 009L P 55



19 009L P 77



19 009L P 46

Scale 1:1



19 009L P 03



19 009L P 00

- Movement:** Hour, Minute, Small Second Hands
Control by 3 Motors
- RF Link:** Connect to IOS and Android mobile phone
- Features:** STOPPER, STEP, TIME/DATE,
TOUCH HEART RATE,
SLEEP & ALARM ALERT
- Stopper:** 1 sec Resolution up to 12 Hours
(Operation by App)
Daily Steps from 1 to 12000 Steps
2 Hands, Hour/Minute/Date/Day/Step
1st to 31st
- Heart Rate:** ECG Finger Touch Heart Rate
works between 40-190BPM
- Sleep Alert:** Piezo Sound (Operation by App)
- Alarm Alert:** Piezo Sound (Operation by App)
- Incoming Phone:** Piezo Sound / LED Flashing
- Incoming Message:** Piezo Sound / LED Flashing
- Battery:** Lithium Battery, CR2025
- Battery Life:** 5 months typ, 8 months Max.
- No. of Button:** 1

SIZE



Battery Caseback



Optical HR Caseback

THICKNESS



11.00mm



12.50mm Optical Heart Rate



19-1007 S 33



19-1007 S 20



19-1007 S 13



19-1007 S 10



19-1007 S 31

Scale 1:1



19-1007 S 33



19-1007 S 22



19-1007 S 21

Scale 1:1



19-1007 S 16




19-1007 S 11

- Movement:** Hour, Minute, Small Second Hands
Control by 3 Motors
- RF Link:** Connect to IOS and Android mobile phone
- Features:** STOPPER, STEP, TIME/DATE,
TOUCH HEART RATE,
SLEEP & ALARM ALERT
- Stopper:** 1 sec Resolution up to 12 Hours
(Operation by App)
- Step:** Daily Steps from 1 to 12000 Steps
- Time:** 2 Hands, Hour/Minute/Date/Day/Step
- Date:** 1st to 31st
- Heart Rate:** ECG Finger Touch Heart Rate
works between 40-190BPM
- Sleep Alert:** Piezo Sound (Operation by App)
- Alarm Alert:** Piezo Sound (Operation by App)
- Incoming Phone:** Piezo Sound / LED Flashing
- Incoming Message:** Piezo Sound / LED Flashing
- Battery:** Lithium Battery, CR2025
- Battery Life:** 5 months typ, 8 months Max.
- No. of Button:** 1

SIZE



THICKNESS





19 009 P 33



19 009 P 30



19 009 P 32



19 009 P 44



19 009 P 40



19 009 P 55



19 009 P 77

Scale 1:1



19 009 P 46



19 009 P 03


Scale 1:1



19 009 P 00

- Movement:** Hour, Minute, Small Second Hands
Control by 3 Motors
- RF Link:** Connect to IOS and Android mobile phone
- Features:** STOPPER, STEP, TIME/DATE,
TOUCH HEART RATE,
SLEEP & ALARM ALERT
- Stopper:** 1 sec Resolution up to 12 Hours
(Operation by App)
Daily Steps from 1 to 12000 Steps
2 Hands, Hour/Minute/Date/Day/Step
1st to 31st
- Heart Rate:** ECG Finger Touch Heart Rate
works between 40-190BPM
- Sleep Alert:** Piezo Sound (Operation by App)
- Alarm Alert:** Piezo Sound (Operation by App)
- Incoming Phone:** Piezo Sound / LED Flashing
- Incoming Message:** Piezo Sound / LED Flashing
- Battery:** Lithium Battery, CR2025
- Battery Life:** 5 months typ, 8 months Max.
- No. of Button:** 1

SIZE



Battery Caseback



Optical HR Caseback

THICKNESS



11.00mm



12.50mm

Optical Heart Rate